

Race helper 3 Operation Instruction

Features

MR-RH3

Digital LCD
Simultaneously displays temperature, Humidity and time with digital LCD
Time and Alarm function
Displays time with alarm function
Two installing methods
Can be placed on the table, nailed on the wall
Basic Specifications and Parameters
Range:Indoor temperature(-30°C~50°C) Humidity(10%~99%)
Celsius - Fahrenheit
Choices of Celsius - Fahrenheit

Accuracy:0.1 C Humidity 1%
Power:One AAA size battery (1.2~1.5V)

Operational Instructions

- Maximum / Minimum Memory
Press key [MEMORY] and hold for a second to store and overwrite MAX/MIN temperature and MAX/MIN humidity.
- Memory Clearing
Press key[RESET] on the back side, and all memory will be cleared.
- Time / Month / Date / Alarm 12 or 24Hour Setting
 - 1.Press[MODE]key and hold 3seconds to enter setting mode.
 - 2.Press[MODE]to select Hour or Minute / Month / Date / Alarm 12/24hour adjustment.
 - 3.Press[ADJ] to adjust values, if pressed long enough, values will be fast adjusted.
- Alarm Setting
 - 1.Press[MODE]to enter alarm setting mode.
 - 2.Press [ADJ] to choose Alarm/Off
 - 3.Press[MODE] and hold one second.
 - 4.Press [ADJ] to adjust H or M, if pressed long enough, H or M will be fast adjusted.
- Month-Date Display
 - 1.Press[ADJ]
 - 2.LCD display will show you Month-Date. Display will be returned to Clock shortly.

The logo for 'Muchmore' is written in a bold, italicized, red font with a black outline and a white drop shadow, giving it a 3D effect.

127-1, Poongdong, Ilsangu,
Goyangcity, Gyeong-gi do,
411-842, Korea
TEL +82 31 903 0487 FAX +82 31 903 0497